LPHA FLOW AMF-2V





The Alpha FLOW Series has been designed to improve comfort and performance whilst maintaining a secure fit. Colour coding the range makes identification simple and easy when varying levels of protection may be required.

FEATURES

- Large surface area ensures very low breathing resistance
- New large exhalation valve which reduces heat build-up and improves wearer comfort
- Colour coded alphamesh shell for ease of identification
- Adjustable headstrap allows for a secure and comfortable fit
- Metal-free suitable for food industry applications
- Preformed nosebridge eliminates the need for regular adjustment
- Compatible with a wide range of safety eyewear
- Soft flexible mesh maintains it's shape and will not collapse during use
- Conforms to EN 149: 2001 + A1: 2009 FFP2 NR



PREFORMED NOSEBRIDGE

Ensures excellent fit without the need to keep adjusting while wearing

EXHALATION VALVE Reduces heat and moisture build-up

NEW MESH DESIGN

Lightweight, flexible and will not collapse during use







ORDERING INFORMATION

Part Number: AMF-2V

Packaging: 10 singles per box

20 boxes per case

Certification: EN149: 2001 + A1: 2009

FFP2 NR

SUITABLE APPLICATIONS

Recommended applications include:

- **Agriculture**
- Construction
- **Food Processing**
- Laboratories
- Metalworking
- **Pharmaceutical**
- **Powdered Chemicals**
- Ship Building/Repair
- Woodworking Industry



LPHA FLOW AMF-2V



P2 DISPOSABLE RESPIRATOR

TECHNICAL SPECIFICATIONS

MATERIALS

COMPONENT	MATERIAL
Mesh Shell:	Polypropylene
Filter Outer Layer:	Polypropylene
Filter Inner Layer:	Polypropylene
Filter Internal Media:	Melt-Blown [Polypropylene]
Headstrap:	Woven Elastic [Latex-Free]
Headstrap Adjuster:	Polypropylene
Exhalation Valve - Valve Housing:	Polypropylene & ABS
Valve Membrane:	Synthetic Rubber

DIMENSIONS

ITEM	LENGTH (mm)	WIDTH (mm)	HEIGHT (mm)	
Respirator	155	70	125	
Nosebridge	25	50	35	
Headband	700	9	0.4	
Headband clip	57	12	9	
Valve	43	43	10	

CERTIFICATION

EC-Type Examination Certification according to European Council Directive 89/686/EEC and subsequent amendments, certified by BSI, Kitemark House, Maylands Ave, Hemel Hempstead HP2 4SQ.

Notified Body: INSPEC International Ltd., 56 Leslie Hough Way, Salford, Greater Manchester, M6 6AJ, UK. [N.B. No. 0194]

RECOMMENDATIONS FOR USE

This respirator is disposable and recommended for single use only.

Do not attempt to clean or re-use.

PRODUCT SELECTOR GUIDANCE CHART

Approval EN 149: 2001 + A1:2009	Mesh Colour	Product Codes	APF (Assigned Protection Factor) (x WEL)	Non-Toxic Dusts	Fine / Toxic Dusts / Mists / Fumes	VeryFine / Toxic Dusts / Mists / Fumes	Odours/ Organic Vapours (Below WEL)	Metal Fumes	Oil/Water Based Particulates
FFP1 NR	White	AMF-1	4						
FFP2 NR	Blue	AMF-2	10	0				0	
FFP2 NR	Blue	AMF-2V	10	0				0	
FFP3 R D ◢	Orange	AMF-3V	20	0		•		0	
FFP3 NR	Grey	AMF-3CV	20	0					

